

1.7 2 3 .020 .100 .500 .05 .10 .20
1.4 5 .005 1.0 .02 1.0 .40
dB:1 RATIO ms/dB ATTACK sec/dB RELEASE

-12 -11 -10 -9 -8 -7 -6 -5 -4 -3 -2
-13 -14 -15 -16 -17 -18 -19 -20 0 +1
dB INPUT GAIN

+7 +8 +9 +10 +11 +12 +13 +14 +15 +16 +17 +18 +19
+6 +5 +4 +3 +2 +1 0 dB OUTPUT GAIN

vu meter g.r. in compressor

Prism Sound
MASELEC MASTER SERIES
MLA-2
precision stereo compressor

1.7 2 3 .020 .100 .500 .05 .10 .20
1.4 5 .005 1.0 .02 1.0 .40
dB:1 RATIO ms/dB ATTACK sec/dB RELEASE

-12 -11 -10 -9 -8 -7 -6 -5 -4 -3 -2
-13 -14 -15 -16 -17 -18 -19 -20 0 +1
dB INPUT GAIN

+7 +8 +9 +10 +11 +12 +13 +14 +15 +16 +17 +18 +19
+6 +5 +4 +3 +2 +1 0 dB OUTPUT GAIN

vu meter g.r. in compressor

off on power
off on link

1.7 2 3 .020 .100 .500 .05 .10 .20
1.4 5 .005 1.0 .02 1.0 .40
dB:1 RATIO ms/dB ATTACK sec/dB RELEASE

-12 -11 -10 -9 -8 -7 -6 -5 -4 -3 -2
-13 -14 -15 -16 -17 -18 -19 -20 0 +1
dB INPUT GAIN

+7 +8 +9 +10 +11 +12 +13 +14 +15 +16 +17 +18 +19
+6 +5 +4 +3 +2 +1 0 dB OUTPUT GAIN

vu meter g.r. in compressor

Prism Sound
MASELEC MASTER SERIES
MLA-2
precision stereo compressor

1.7 2 3 .020 .100 .500 .05 .10 .20
1.4 5 .005 1.0 .02 1.0 .40
dB:1 RATIO ms/dB ATTACK sec/dB RELEASE

-12 -11 -10 -9 -8 -7 -6 -5 -4 -3 -2
-13 -14 -15 -16 -17 -18 -19 -20 0 +1
dB INPUT GAIN

+7 +8 +9 +10 +11 +12 +13 +14 +15 +16 +17 +18 +19
+6 +5 +4 +3 +2 +1 0 dB OUTPUT GAIN

vu meter g.r. in compressor

off on power
off on link
